



**Product Change Notification**

**CN-202605004F**

**Issue date:** 23 Jul 2026

**Effective date:** 13 Aug 2026

Dear [pcn@ttiinc.com](mailto:pcn@ttiinc.com),

Here's your personalized quality information concerning products our customers and partners purchased from Nexperia.

For more details please contact your respective Nexperia CSR/AM.



**Extraordinary PCN: Release of additional assembly site ATSN due to exceptional circumstances outside the control of Nexperia B.V. for SOD523**

**Change  
Category**

|                                    |                                              |                                                    |                                          |                                     |
|------------------------------------|----------------------------------------------|----------------------------------------------------|------------------------------------------|-------------------------------------|
| <input type="checkbox"/> Wafer     | <input type="checkbox"/> Assembly            |                                                    | <input checked="" type="checkbox"/> Test |                                     |
| <input type="checkbox"/> Fab       | Process                                      | <input type="checkbox"/> Product Marking           | Location                                 | <input type="checkbox"/> Design     |
| <input type="checkbox"/> Process   | <input type="checkbox"/> Assembly            | <input checked="" type="checkbox"/> Mechanical     | <input type="checkbox"/> Test            | <input type="checkbox"/> Errata     |
|                                    | Materials                                    | Specification                                      | Process                                  | <input type="checkbox"/> Electrical |
| <input type="checkbox"/> Wafer     | <input checked="" type="checkbox"/> Assembly | <input type="checkbox"/> Packing/Shipping/Labeling | <input type="checkbox"/> Test            | spec./Test                          |
| <input type="checkbox"/> Fab       | Location                                     |                                                    | Equipment                                | coverage                            |
| <input type="checkbox"/> Materials |                                              |                                                    |                                          |                                     |

[ ] Wafer  
Fab  
Location

### Details of this change

The Nexperia owned assembly site ATSN will be released additionally for production with immediate effect. The materials and electrical specifications of the products remain unchanged.

The SOD523 product drawing is updated by changing minor dimensions.

CN-202605004F-productchangematrix.xlsx:

<https://qcm.nexperia.com/Document/DOC-614237/CN-202605004F-productchangematrix.xlsx>

CN-202605004F-PCN-FORM-Rev.xlsm:

<https://qcm.nexperia.com/Document/DOC-614236/CN-202605004F-PCN-FORM-Rev.xlsm>

CN-202605004F-PCN-Delta-Qualification-Matrix.xlsm:

<https://qcm.nexperia.com/Document/DOC-614235/CN-202605004F-PCN-Delta-Qualification-Matrix.xlsm>

CN-202605004F-SQR.pdf: <https://qcm.nexperia.com/Document/DOC-614234/CN-202605004F-SQR.pdf>

### Why do we implement this change?

Exceptional circumstances outside the control of Nexperia B.V. regarding the test and assembly site ATGD in Dongguan, China are continuing to impact our supply chain. To ensure future supply and minimize disruption, we release the Nexperia B.V. owned assembly site ATSN in Seremban, Malaysia as an additional assembly site with immediate effect.

Impact and Required Action:

- New orders for the affected 12NCs will automatically be considered as acceptance of this PCN.

- If you do not agree with the changes described in this PCN, please let us know immediately and ensure no new orders for the affected products are placed. If we do not receive a response from you within five (5) working days from the date of this PCN notification, we will assume that you accept the PCN.
- In case of a rejection of the PCN, Nexperia B.V. will reserve the right to cancel all open and confirmed orders related to the affected product(s) and as such a rejection may result in discontinuation of supply. Nexperia B.V. cannot be held liable for non-supply in such cases.

### **Identification of affected products**

The assembly site can be identified on the packing labels (outer box as well as reel-label).

### **Management summary**

Release of additional assembly site ATSN (Seremban, Malaysia) for SOD523

### **Product availability**

### **Production**

Planned first shipment: 13 Aug 2026

Existing inventory will be shipped until depleted

### **Sample information**

Please see remarks for sample availability

### **Impact**

No impact to the product's functionality anticipated

## Data sheet revision

A new datasheet will be issued

## Feedback

Your acknowledgement of this change, conform JEDEC J-STD-046, is expected till 06 Aug 2026. Lack of acknowledgement of the PCN constitutes acceptance of the change.

## Additional information

[View Change Notification Online](#)

## Remarks

Please note that currently active PCNs are not affected by this notification. They remain valid and need to be released according to JEDEC requirements. This PCN only adds ATSN as a qualified assembly site. All running PCNs can be found in the Product Change Matrix. Please note that PCN sample requests for Extraordinary PCNs cannot be supported. There is no dedicated PCN sample step in this expedited process. Samples will become available after mass production start via our eSample Store, please contact your local Nexperia Sales Support Team.

## Contact and support

For all Quality Notification content inquiries, please contact your local Nexperia Sales Support Team.

For specific questions on this notice or the products affected please contact our specialist directly: [pcn@nexperia.com](mailto:pcn@nexperia.com)

In case of distribution, please contact you distribution partner.

## About Nexperia B.V.

We at Nexperia are the efficiency semiconductor company. We deliver over 90 billion products a year and as such service thousands of global customers, both directly and through our extensive network of channel partners. We are at the heart of billions of electronic devices in the Automotive, Mobile, Industrial, Consumer, Computing, and Communication Infrastructure segments.

You have received this email because you are a designated contact or subscribed to Nexperia Quality Notifications. Nexperia shall not be held liable if this Notification is not correctly distributed within your organization.

This message has been automatically distributed. Please do not reply.

If you would like to adjust your mailing preferences, please click [here](#).

| SalesItem_name | SalesItem_orderablePartNumber | SalesOrder_customerPartNumber | ProductType_name |
|----------------|-------------------------------|-------------------------------|------------------|
| 934054914115   | 1PS79SB10,115                 |                               | 1PS79SB10        |
| 934669827115   | 1PS79SB10-QX                  |                               | 1PS79SB10-Q      |
| 934054914315   | 1PS79SB10X                    | 1PS79SB10X                    | 1PS79SB10        |
| 934056394115   | 1PS79SB30,115                 |                               | 1PS79SB30        |
| 934056394135   | 1PS79SB30,135                 |                               | 1PS79SB30        |
| 934664799135   | 1PS79SB30-QF                  |                               | 1PS79SB30-Q      |
| 934664799115   | 1PS79SB30-QX                  |                               | 1PS79SB30-Q      |
| 934056394315   | 1PS79SB30YL                   |                               | 1PS79SB30        |
| 934056795115   | 1PS79SB31,115                 | 1PS79SB31,115                 | 1PS79SB31        |
| 934056795135   | 1PS79SB31,135                 |                               | 1PS79SB31        |
| 934056795315   | 1PS79SB31,315                 |                               | 1PS79SB31        |
| 934664931135   | 1PS79SB31-QF                  |                               | 1PS79SB31-Q      |
| 934664931115   | 1PS79SB31-QX                  |                               | 1PS79SB31-Q      |
| 934055508115   | 1PS79SB40,115                 |                               | 1PS79SB40        |
| 934669622115   | 1PS79SB40-QX                  |                               | 1PS79SB40-Q      |
| 934054924115   | 1PS79SB70,115                 |                               | 1PS79SB70        |
| 934054924315   | 1PS79SB70,315                 |                               | 1PS79SB70        |
| 934664500115   | 1PS79SB70-QX                  | 1PS79SB70-QX                  | 1PS79SB70-Q      |
| 934664500315   | 1PS79SB70-QYL                 |                               | 1PS79SB70-Q      |
| 934055217115   | BAS516,115                    | BAS516,115                    | BAS516           |
| 934055217135   | BAS516,135                    |                               | BAS516           |
| 934055217315   | BAS516,315                    |                               | BAS516           |
| 934663912135   | BAS516-QF                     |                               | BAS516-Q         |
| 934663912115   | BAS516-QX                     |                               | BAS516-Q         |
| 934663912315   | BAS516-QYL                    |                               | BAS516-Q         |
| 934057766115   | BAS521,115                    |                               | BAS521           |
| 934057766135   | BAS521,135                    |                               | BAS521           |
| 934057766315   | BAS521,315                    |                               | BAS521           |
| 934662966135   | BAS521-QF                     |                               | BAS521-Q         |
| 934662966115   | BAS521-QX                     | BAS521-QX                     | BAS521-Q         |
| 934662966315   | BAS521-QYL                    |                               | BAS521-Q         |
| 934667689135   | BAS521B-QF                    |                               | BAS521B-Q        |
| 934667689115   | BAS521B-QX                    |                               | BAS521B-Q        |
| 934660344135   | BAS521BF                      |                               | BAS521B          |
| 934660344115   | BAS521BX                      |                               | BAS521B          |
| 934057972115   | BAS716,115                    | BAS716,115                    | BAS716           |
| 934669574115   | BAS716-QX                     |                               | BAS716-Q         |
| 934057972135   | BAS716F                       |                               | BAS716           |
| 934057972315   | BAS716YL                      |                               | BAS716           |
| 934055871115   | BZX585-B10,115                |                               | BZX585-B10       |
| 934055871135   | BZX585-B10,135                |                               | BZX585-B10       |
| 934667479115   | BZX585-B10-QX                 |                               | BZX585-B10-Q     |
| 934055872115   | BZX585-B11,115                |                               | BZX585-B11       |
| 934055872135   | BZX585-B11,135                |                               | BZX585-B11       |
| 934667481115   | BZX585-B11-QX                 |                               | BZX585-B11-Q     |
| 934055873115   | BZX585-B12,115                |                               | BZX585-B12       |
| 934055873135   | BZX585-B12,135                |                               | BZX585-B12       |

|              |                 |                 |               |
|--------------|-----------------|-----------------|---------------|
| 934667482115 | BZX585-B12-QX   |                 | BZX585-B12-Q  |
| 934055874115 | BZX585-B13,115  |                 | BZX585-B13    |
| 934055874135 | BZX585-B13,135  |                 | BZX585-B13    |
| 934667483115 | BZX585-B13-QX   |                 | BZX585-B13-Q  |
| 934055875115 | BZX585-B15,115  |                 | BZX585-B15    |
| 934055875135 | BZX585-B15,135  |                 | BZX585-B15    |
| 934667485115 | BZX585-B15-QX   |                 | BZX585-B15-Q  |
| 934057404115 | BZX585-B16,115  | BZX585-B16,115  | BZX585-B16    |
| 934667486115 | BZX585-B16-QX   |                 | BZX585-B16-Q  |
| 934057405115 | BZX585-B18,115  |                 | BZX585-B18    |
| 934667487115 | BZX585-B18-QX   |                 | BZX585-B18-Q  |
| 934057406115 | BZX585-B20,115  |                 | BZX585-B20    |
| 934667488115 | BZX585-B20-QX   |                 | BZX585-B20-Q  |
| 934057407115 | BZX585-B22,115  |                 | BZX585-B22    |
| 934667489115 | BZX585-B22-QX   |                 | BZX585-B22-Q  |
| 934057408115 | BZX585-B24,115  |                 | BZX585-B24    |
| 934667490115 | BZX585-B24-QX   |                 | BZX585-B24-Q  |
| 934057410115 | BZX585-B27,115  |                 | BZX585-B27    |
| 934667491115 | BZX585-B27-QX   |                 | BZX585-B27-Q  |
| 934055856115 | BZX585-B2V4,115 |                 | BZX585-B2V4   |
| 934055856135 | BZX585-B2V4,135 |                 | BZX585-B2V4   |
| 934667464115 | BZX585-B2V4-QX  |                 | BZX585-B2V4-Q |
| 934055857115 | BZX585-B2V7,115 |                 | BZX585-B2V7   |
| 934055857135 | BZX585-B2V7,135 |                 | BZX585-B2V7   |
| 934667465115 | BZX585-B2V7-QX  |                 | BZX585-B2V7-Q |
| 934057409115 | BZX585-B30,115  | BZX585-B30,115  | BZX585-B30    |
| 934667492115 | BZX585-B30-QX   |                 | BZX585-B30-Q  |
| 934057411115 | BZX585-B33,115  |                 | BZX585-B33    |
| 934667493115 | BZX585-B33-QX   |                 | BZX585-B33-Q  |
| 934057412115 | BZX585-B36,115  |                 | BZX585-B36    |
| 934667497115 | BZX585-B36-QX   |                 | BZX585-B36-Q  |
| 934057413115 | BZX585-B39,115  |                 | BZX585-B39    |
| 934667498115 | BZX585-B39-QX   |                 | BZX585-B39-Q  |
| 934055858115 | BZX585-B3V0,115 |                 | BZX585-B3V0   |
| 934055858135 | BZX585-B3V0,135 |                 | BZX585-B3V0   |
| 934667466115 | BZX585-B3V0-QX  |                 | BZX585-B3V0-Q |
| 934055859115 | BZX585-B3V3,115 |                 | BZX585-B3V3   |
| 934055859135 | BZX585-B3V3,135 |                 | BZX585-B3V3   |
| 934667467115 | BZX585-B3V3-QX  |                 | BZX585-B3V3-Q |
| 934055860115 | BZX585-B3V6,115 | BZX585-B3V6,115 | BZX585-B3V6   |
| 934055860135 | BZX585-B3V6,135 |                 | BZX585-B3V6   |
| 934667468115 | BZX585-B3V6-QX  |                 | BZX585-B3V6-Q |
| 934055861115 | BZX585-B3V9,115 |                 | BZX585-B3V9   |
| 934055861135 | BZX585-B3V9,135 |                 | BZX585-B3V9   |
| 934667469115 | BZX585-B3V9-QX  |                 | BZX585-B3V9-Q |
| 934057414115 | BZX585-B43,115  |                 | BZX585-B43    |
| 934667499115 | BZX585-B43-QX   |                 | BZX585-B43-Q  |
| 934057415115 | BZX585-B47,115  |                 | BZX585-B47    |

|              |                 |               |
|--------------|-----------------|---------------|
| 934667500115 | BZX585-B47-QX   | BZX585-B47-Q  |
| 934055862115 | BZX585-B4V3,115 | BZX585-B4V3   |
| 934055862135 | BZX585-B4V3,135 | BZX585-B4V3   |
| 934667470115 | BZX585-B4V3-QX  | BZX585-B4V3-Q |
| 934055863115 | BZX585-B4V7,115 | BZX585-B4V7   |
| 934055863135 | BZX585-B4V7,135 | BZX585-B4V7   |
| 934667471115 | BZX585-B4V7-QX  | BZX585-B4V7-Q |
| 934057416115 | BZX585-B51,115  | BZX585-B51    |
| 934667501115 | BZX585-B51-QX   | BZX585-B51-Q  |
| 934057417115 | BZX585-B56,115  | BZX585-B56    |
| 934667502115 | BZX585-B56-QX   | BZX585-B56-Q  |
| 934055864115 | BZX585-B5V1,115 | BZX585-B5V1   |
| 934055864135 | BZX585-B5V1,135 | BZX585-B5V1   |
| 934667472115 | BZX585-B5V1-QX  | BZX585-B5V1-Q |
| 934055865115 | BZX585-B5V6,115 | BZX585-B5V6   |
| 934055865135 | BZX585-B5V6,135 | BZX585-B5V6   |
| 934667473115 | BZX585-B5V6-QX  | BZX585-B5V6-Q |
| 934057418115 | BZX585-B62,115  | BZX585-B62    |
| 934667503115 | BZX585-B62-QX   | BZX585-B62-Q  |
| 934057419115 | BZX585-B68,115  | BZX585-B68    |
| 934667504115 | BZX585-B68-QX   | BZX585-B68-Q  |
| 934055866115 | BZX585-B6V2,115 | BZX585-B6V2   |
| 934055866135 | BZX585-B6V2,135 | BZX585-B6V2   |
| 934667474115 | BZX585-B6V2-QX  | BZX585-B6V2-Q |
| 934055867115 | BZX585-B6V8,115 | BZX585-B6V8   |
| 934055867135 | BZX585-B6V8,135 | BZX585-B6V8   |
| 934667475115 | BZX585-B6V8-QX  | BZX585-B6V8-Q |
| 934057420115 | BZX585-B75,115  | BZX585-B75    |
| 934667505115 | BZX585-B75-QX   | BZX585-B75-Q  |
| 934055868115 | BZX585-B7V5,115 | BZX585-B7V5   |
| 934055868135 | BZX585-B7V5,135 | BZX585-B7V5   |
| 934667476115 | BZX585-B7V5-QX  | BZX585-B7V5-Q |
| 934055869115 | BZX585-B8V2,115 | BZX585-B8V2   |
| 934055869135 | BZX585-B8V2,135 | BZX585-B8V2   |
| 934667477115 | BZX585-B8V2-QX  | BZX585-B8V2-Q |
| 934055870115 | BZX585-B9V1,115 | BZX585-B9V1   |
| 934055870135 | BZX585-B9V1,135 | BZX585-B9V1   |
| 934667478115 | BZX585-B9V1-QX  | BZX585-B9V1-Q |
| 934055851115 | BZX585-C10,115  | BZX585-C10    |
| 934055851135 | BZX585-C10,135  | BZX585-C10    |
| 934667433115 | BZX585-C10-QX   | BZX585-C10-Q  |
| 934055852115 | BZX585-C11,115  | BZX585-C11    |
| 934055852135 | BZX585-C11,135  | BZX585-C11    |
| 934667434115 | BZX585-C11-QX   | BZX585-C11-Q  |
| 934055852315 | BZX585-C11YL    | BZX585-C11    |
| 934055853115 | BZX585-C12,115  | BZX585-C12    |
| 934055853135 | BZX585-C12,135  | BZX585-C12    |
| 934667435135 | BZX585-C12-QF   | BZX585-C12-Q  |

|              |                 |                 |               |
|--------------|-----------------|-----------------|---------------|
| 934667435115 | BZX585-C12-QX   |                 | BZX585-C12-Q  |
| 934055854115 | BZX585-C13,115  |                 | BZX585-C13    |
| 934055854135 | BZX585-C13,135  |                 | BZX585-C13    |
| 934667436135 | BZX585-C13-QF   |                 | BZX585-C13-Q  |
| 934667436115 | BZX585-C13-QX   |                 | BZX585-C13-Q  |
| 934055854315 | BZX585-C13F     |                 | BZX585-C13    |
| 934055855115 | BZX585-C15,115  |                 | BZX585-C15    |
| 934055855135 | BZX585-C15,135  | BZX585-C15,135  | BZX585-C15    |
| 934667388115 | BZX585-C15-QX   |                 | BZX585-C15-Q  |
| 934057421115 | BZX585-C16,115  |                 | BZX585-C16    |
| 934667404115 | BZX585-C16-QX   |                 | BZX585-C16-Q  |
| 934057422115 | BZX585-C18,115  | BZX585-C18,115  | BZX585-C18    |
| 934663906115 | BZX585-C18-QX   |                 | BZX585-C18-Q  |
| 934057423115 | BZX585-C20,115  |                 | BZX585-C20    |
| 934667407115 | BZX585-C20-QX   |                 | BZX585-C20-Q  |
| 934057424115 | BZX585-C22,115  |                 | BZX585-C22    |
| 934667410115 | BZX585-C22-QX   |                 | BZX585-C22-Q  |
| 934057425115 | BZX585-C24,115  |                 | BZX585-C24    |
| 934667411115 | BZX585-C24-QX   |                 | BZX585-C24-Q  |
| 934057426115 | BZX585-C27,115  |                 | BZX585-C27    |
| 934667412115 | BZX585-C27-QX   |                 | BZX585-C27-Q  |
| 934661811135 | BZX585-C27/1F   |                 | BZX585-C27/1  |
| 934661811115 | BZX585-C27/1X   |                 | BZX585-C27/1  |
| 934057426135 | BZX585-C27F     |                 | BZX585-C27    |
| 934055836115 | BZX585-C2V4,115 |                 | BZX585-C2V4   |
| 934055836135 | BZX585-C2V4,135 |                 | BZX585-C2V4   |
| 934667386115 | BZX585-C2V4-QX  |                 | BZX585-C2V4-Q |
| 934055837115 | BZX585-C2V7,115 |                 | BZX585-C2V7   |
| 934055837135 | BZX585-C2V7,135 |                 | BZX585-C2V7   |
| 934667419115 | BZX585-C2V7-QX  |                 | BZX585-C2V7-Q |
| 934057427115 | BZX585-C30,115  |                 | BZX585-C30    |
| 934667413115 | BZX585-C30-QX   |                 | BZX585-C30-Q  |
| 934057428115 | BZX585-C33,115  |                 | BZX585-C33    |
| 934667414115 | BZX585-C33-QX   |                 | BZX585-C33-Q  |
| 934057429115 | BZX585-C36,115  |                 | BZX585-C36    |
| 934667415115 | BZX585-C36-QX   |                 | BZX585-C36-Q  |
| 934057429135 | BZX585-C36F     |                 | BZX585-C36    |
| 934057430115 | BZX585-C39,115  |                 | BZX585-C39    |
| 934667416115 | BZX585-C39-QX   |                 | BZX585-C39-Q  |
| 934055838115 | BZX585-C3V0,115 | BZX585-C3V0,115 | BZX585-C3V0   |
| 934055838135 | BZX585-C3V0,135 | BZX585-C3V0,135 | BZX585-C3V0   |
| 934667420135 | BZX585-C3V0-QF  |                 | BZX585-C3V0-Q |
| 934667420115 | BZX585-C3V0-QX  |                 | BZX585-C3V0-Q |
| 934055839115 | BZX585-C3V3,115 |                 | BZX585-C3V3   |
| 934055839135 | BZX585-C3V3,135 |                 | BZX585-C3V3   |
| 934667421115 | BZX585-C3V3-QX  |                 | BZX585-C3V3-Q |
| 934055840115 | BZX585-C3V6,115 | BZX585-C3V6,115 | BZX585-C3V6   |
| 934055840135 | BZX585-C3V6,135 |                 | BZX585-C3V6   |

|              |                 |                |
|--------------|-----------------|----------------|
| 934667422115 | BZX585-C3V6-QX  | BZX585-C3V6-Q  |
| 934055841115 | BZX585-C3V9,115 | BZX585-C3V9    |
| 934055841135 | BZX585-C3V9,135 | BZX585-C3V9    |
| 934667423115 | BZX585-C3V9-QX  | BZX585-C3V9-Q  |
| 934057431115 | BZX585-C43,115  | BZX585-C43     |
| 934667417115 | BZX585-C43-QX   | BZX585-C43-Q   |
| 934057432115 | BZX585-C47,115  | BZX585-C47     |
| 934667418115 | BZX585-C47-QX   | BZX585-C47-Q   |
| 934055842115 | BZX585-C4V3,115 | BZX585-C4V3    |
| 934055842135 | BZX585-C4V3,135 | BZX585-C4V3    |
| 934667424115 | BZX585-C4V3-QX  | BZX585-C4V3-Q  |
| 934055843115 | BZX585-C4V7,115 | BZX585-C4V7    |
| 934055843135 | BZX585-C4V7,135 | BZX585-C4V7    |
| 934667425135 | BZX585-C4V7-QF  | BZX585-C4V7-Q  |
| 934667425115 | BZX585-C4V7-QX  | BZX585-C4V7-Q  |
| 934057433115 | BZX585-C51,115  | BZX585-C51     |
| 934667437115 | BZX585-C51-QX   | BZX585-C51-Q   |
| 934057434115 | BZX585-C56,115  | BZX585-C56     |
| 934667438115 | BZX585-C56-QX   | BZX585-C56-Q   |
| 934055844115 | BZX585-C5V1,115 | BZX585-C5V1    |
| 934055844135 | BZX585-C5V1,135 | BZX585-C5V1    |
| 934667426115 | BZX585-C5V1-QX  | BZX585-C5V1-Q  |
| 934055845115 | BZX585-C5V6,115 | BZX585-C5V6    |
| 934055845135 | BZX585-C5V6,135 | BZX585-C5V6    |
| 934667427115 | BZX585-C5V6-QX  | BZX585-C5V6-Q  |
| 934057435115 | BZX585-C62,115  | BZX585-C62     |
| 934667439115 | BZX585-C62-QX   | BZX585-C62-Q   |
| 934057436115 | BZX585-C68,115  | BZX585-C68     |
| 934667440115 | BZX585-C68-QX   | BZX585-C68-Q   |
| 934055846115 | BZX585-C6V2,115 | BZX585-C6V2    |
| 934055846135 | BZX585-C6V2,135 | BZX585-C6V2    |
| 934667428115 | BZX585-C6V2-QX  | BZX585-C6V2-Q  |
| 934055847115 | BZX585-C6V8,115 | BZX585-C6V8    |
| 934055847135 | BZX585-C6V8,135 | BZX585-C6V8    |
| 934667429115 | BZX585-C6V8-QX  | BZX585-C6V8-Q  |
| 934057437115 | BZX585-C75,115  | BZX585-C75     |
| 934667441115 | BZX585-C75-QX   | BZX585-C75-Q   |
| 934055848115 | BZX585-C7V5,115 | BZX585-C7V5    |
| 934055848135 | BZX585-C7V5,135 | BZX585-C7V5    |
| 934667430115 | BZX585-C7V5-QX  | BZX585-C7V5-Q  |
| 934055849115 | BZX585-C8V2,115 | BZX585-C8V2    |
| 934055849135 | BZX585-C8V2,135 | BZX585-C8V2    |
| 934667431115 | BZX585-C8V2-QX  | BZX585-C8V2-Q  |
| 934055850115 | BZX585-C9V1,115 | BZX585-C9V1    |
| 934055850135 | BZX585-C9V1,135 | BZX585-C9V1    |
| 934667432135 | BZX585-C9V1-QF  | BZX585-C9V1-Q  |
| 934667432115 | BZX585-C9V1-QX  | BZX585-C9V1-Q  |
| 934666386115 | BZX58550-B10-QX | BZX58550-B10-Q |

BZX585-C8V2,135

|              |                  |                 |
|--------------|------------------|-----------------|
| 934666199115 | BZX58550-B10X    | BZX58550-B10    |
| 934666387115 | BZX58550-B11-QX  | BZX58550-B11-Q  |
| 934666200115 | BZX58550-B11X    | BZX58550-B11    |
| 934666388115 | BZX58550-B12-QX  | BZX58550-B12-Q  |
| 934666201115 | BZX58550-B12X    | BZX58550-B12    |
| 934666389115 | BZX58550-B13-QX  | BZX58550-B13-Q  |
| 934666202115 | BZX58550-B13X    | BZX58550-B13    |
| 934666390115 | BZX58550-B15-QX  | BZX58550-B15-Q  |
| 934666203115 | BZX58550-B15X    | BZX58550-B15    |
| 934666391115 | BZX58550-B16-QX  | BZX58550-B16-Q  |
| 934666204115 | BZX58550-B16X    | BZX58550-B16    |
| 934666392115 | BZX58550-B18-QX  | BZX58550-B18-Q  |
| 934666205115 | BZX58550-B18X    | BZX58550-B18    |
| 934666368115 | BZX58550-B1V8-QX | BZX58550-B1V8-Q |
| 934666141115 | BZX58550-B1V8X   | BZX58550-B1V8   |
| 934666393115 | BZX58550-B20-QX  | BZX58550-B20-Q  |
| 934666206115 | BZX58550-B20X    | BZX58550-B20    |
| 934666394115 | BZX58550-B22-QX  | BZX58550-B22-Q  |
| 934666207115 | BZX58550-B22X    | BZX58550-B22    |
| 934666395115 | BZX58550-B24-QX  | BZX58550-B24-Q  |
| 934666208115 | BZX58550-B24X    | BZX58550-B24    |
| 934666396115 | BZX58550-B27-QX  | BZX58550-B27-Q  |
| 934666209115 | BZX58550-B27X    | BZX58550-B27    |
| 934666369115 | BZX58550-B2V0-QX | BZX58550-B2V0-Q |
| 934666142115 | BZX58550-B2V0X   | BZX58550-B2V0   |
| 934666370115 | BZX58550-B2V2-QX | BZX58550-B2V2-Q |
| 934666143115 | BZX58550-B2V2X   | BZX58550-B2V2   |
| 934666371115 | BZX58550-B2V4-QX | BZX58550-B2V4-Q |
| 934666184115 | BZX58550-B2V4X   | BZX58550-B2V4   |
| 934666372115 | BZX58550-B2V7-QX | BZX58550-B2V7-Q |
| 934666185115 | BZX58550-B2V7X   | BZX58550-B2V7   |
| 934666397115 | BZX58550-B30-QX  | BZX58550-B30-Q  |
| 934666210115 | BZX58550-B30X    | BZX58550-B30    |
| 934666398115 | BZX58550-B33-QX  | BZX58550-B33-Q  |
| 934666211115 | BZX58550-B33X    | BZX58550-B33    |
| 934666399115 | BZX58550-B36-QX  | BZX58550-B36-Q  |
| 934666212115 | BZX58550-B36X    | BZX58550-B36    |
| 934666400115 | BZX58550-B39-QX  | BZX58550-B39-Q  |
| 934666213115 | BZX58550-B39X    | BZX58550-B39    |
| 934666373115 | BZX58550-B3V0-QX | BZX58550-B3V0-Q |
| 934666186115 | BZX58550-B3V0X   | BZX58550-B3V0   |
| 934666374115 | BZX58550-B3V3-QX | BZX58550-B3V3-Q |
| 934666187115 | BZX58550-B3V3X   | BZX58550-B3V3   |
| 934666375115 | BZX58550-B3V6-QX | BZX58550-B3V6-Q |
| 934666188115 | BZX58550-B3V6X   | BZX58550-B3V6   |
| 934666376115 | BZX58550-B3V9-QX | BZX58550-B3V9-Q |
| 934666189115 | BZX58550-B3V9X   | BZX58550-B3V9   |
| 934666401115 | BZX58550-B43-QX  | BZX58550-B43-Q  |

|              |                  |               |                 |
|--------------|------------------|---------------|-----------------|
| 934666214115 | BZX58550-B43X    |               | BZX58550-B43    |
| 934666402115 | BZX58550-B47-QX  |               | BZX58550-B47-Q  |
| 934666215115 | BZX58550-B47X    |               | BZX58550-B47    |
| 934666377115 | BZX58550-B4V3-QX |               | BZX58550-B4V3-Q |
| 934666190115 | BZX58550-B4V3X   |               | BZX58550-B4V3   |
| 934666378115 | BZX58550-B4V7-QX |               | BZX58550-B4V7-Q |
| 934666191115 | BZX58550-B4V7X   |               | BZX58550-B4V7   |
| 934666403115 | BZX58550-B51-QX  |               | BZX58550-B51-Q  |
| 934666216115 | BZX58550-B51X    |               | BZX58550-B51    |
| 934666379115 | BZX58550-B5V1-QX |               | BZX58550-B5V1-Q |
| 934666192115 | BZX58550-B5V1X   |               | BZX58550-B5V1   |
| 934666380115 | BZX58550-B5V6-QX |               | BZX58550-B5V6-Q |
| 934666193115 | BZX58550-B5V6X   |               | BZX58550-B5V6   |
| 934666381115 | BZX58550-B6V2-QX |               | BZX58550-B6V2-Q |
| 934666194115 | BZX58550-B6V2X   |               | BZX58550-B6V2   |
| 934666382115 | BZX58550-B6V8-QX |               | BZX58550-B6V8-Q |
| 934666195115 | BZX58550-B6V8X   |               | BZX58550-B6V8   |
| 934666383115 | BZX58550-B7V5-QX |               | BZX58550-B7V5-Q |
| 934666196115 | BZX58550-B7V5X   |               | BZX58550-B7V5   |
| 934666384115 | BZX58550-B8V2-QX |               | BZX58550-B8V2-Q |
| 934666197115 | BZX58550-B8V2X   |               | BZX58550-B8V2   |
| 934666385115 | BZX58550-B9V1-QX |               | BZX58550-B9V1-Q |
| 934666198115 | BZX58550-B9V1X   |               | BZX58550-B9V1   |
| 934663445115 | BZX58550-C10-QX  |               | BZX58550-C10-Q  |
| 934662183115 | BZX58550-C10X    |               | BZX58550-C10    |
| 934663446115 | BZX58550-C11-QX  |               | BZX58550-C11-Q  |
| 934662184115 | BZX58550-C11X    |               | BZX58550-C11    |
| 934663447115 | BZX58550-C12-QX  |               | BZX58550-C12-Q  |
| 934662185115 | BZX58550-C12X    | BZX58550-C12X | BZX58550-C12    |
| 934663448115 | BZX58550-C13-QX  |               | BZX58550-C13-Q  |
| 934662186115 | BZX58550-C13X    |               | BZX58550-C13    |
| 934663449115 | BZX58550-C15-QX  |               | BZX58550-C15-Q  |
| 934662187115 | BZX58550-C15X    |               | BZX58550-C15    |
| 934663450115 | BZX58550-C16-QX  |               | BZX58550-C16-Q  |
| 934662188115 | BZX58550-C16X    |               | BZX58550-C16    |
| 934663451115 | BZX58550-C18-QX  |               | BZX58550-C18-Q  |
| 934662189115 | BZX58550-C18X    |               | BZX58550-C18    |
| 934663427115 | BZX58550-C1V8-QX |               | BZX58550-C1V8-Q |
| 934662163115 | BZX58550-C1V8X   |               | BZX58550-C1V8   |
| 934663452115 | BZX58550-C20-QX  |               | BZX58550-C20-Q  |
| 934662191115 | BZX58550-C20X    |               | BZX58550-C20    |
| 934663454115 | BZX58550-C22-QX  |               | BZX58550-C22-Q  |
| 934662192115 | BZX58550-C22X    |               | BZX58550-C22    |
| 934663455115 | BZX58550-C24-QX  |               | BZX58550-C24-Q  |
| 934662193115 | BZX58550-C24X    |               | BZX58550-C24    |
| 934663456115 | BZX58550-C27-QX  |               | BZX58550-C27-Q  |
| 934662194115 | BZX58550-C27X    |               | BZX58550-C27    |
| 934663428115 | BZX58550-C2V0-QX |               | BZX58550-C2V0-Q |

|              |                  |                 |
|--------------|------------------|-----------------|
| 934662164115 | BZX58550-C2V0X   | BZX58550-C2V0   |
| 934663429115 | BZX58550-C2V2-QX | BZX58550-C2V2-Q |
| 934662165115 | BZX58550-C2V2X   | BZX58550-C2V2   |
| 934663430115 | BZX58550-C2V4-QX | BZX58550-C2V4-Q |
| 934662166115 | BZX58550-C2V4X   | BZX58550-C2V4   |
| 934663431115 | BZX58550-C2V7-QX | BZX58550-C2V7-Q |
| 934662167115 | BZX58550-C2V7X   | BZX58550-C2V7   |
| 934663458115 | BZX58550-C30-QX  | BZX58550-C30-Q  |
| 934662195115 | BZX58550-C30X    | BZX58550-C30    |
| 934663459115 | BZX58550-C33-QX  | BZX58550-C33-Q  |
| 934662196115 | BZX58550-C33X    | BZX58550-C33    |
| 934663460115 | BZX58550-C36-QX  | BZX58550-C36-Q  |
| 934662197115 | BZX58550-C36X    | BZX58550-C36    |
| 934663461115 | BZX58550-C39-QX  | BZX58550-C39-Q  |
| 934662198115 | BZX58550-C39X    | BZX58550-C39    |
| 934663432115 | BZX58550-C3V0-QX | BZX58550-C3V0-Q |
| 934662168115 | BZX58550-C3V0X   | BZX58550-C3V0   |
| 934663433115 | BZX58550-C3V3-QX | BZX58550-C3V3-Q |
| 934662169115 | BZX58550-C3V3X   | BZX58550-C3V3   |
| 934663434115 | BZX58550-C3V6-QX | BZX58550-C3V6-Q |
| 934662171115 | BZX58550-C3V6X   | BZX58550-C3V6   |
| 934663435115 | BZX58550-C3V9-QX | BZX58550-C3V9-Q |
| 934662172115 | BZX58550-C3V9X   | BZX58550-C3V9   |
| 934663462115 | BZX58550-C43-QX  | BZX58550-C43-Q  |
| 934662199115 | BZX58550-C43X    | BZX58550-C43    |
| 934663463115 | BZX58550-C47-QX  | BZX58550-C47-Q  |
| 934662201115 | BZX58550-C47X    | BZX58550-C47    |
| 934663436115 | BZX58550-C4V3-QX | BZX58550-C4V3-Q |
| 934662173115 | BZX58550-C4V3X   | BZX58550-C4V3   |
| 934663437115 | BZX58550-C4V7-QX | BZX58550-C4V7-Q |
| 934662174115 | BZX58550-C4V7X   | BZX58550-C4V7   |
| 934663464115 | BZX58550-C51-QX  | BZX58550-C51-Q  |
| 934662202115 | BZX58550-C51X    | BZX58550-C51    |
| 934663438115 | BZX58550-C5V1-QX | BZX58550-C5V1-Q |
| 934662175115 | BZX58550-C5V1X   | BZX58550-C5V1   |
| 934663439115 | BZX58550-C5V6-QX | BZX58550-C5V6-Q |
| 934662176115 | BZX58550-C5V6X   | BZX58550-C5V6   |
| 934663440115 | BZX58550-C6V2-QX | BZX58550-C6V2-Q |
| 934662177115 | BZX58550-C6V2X   | BZX58550-C6V2   |
| 934663441115 | BZX58550-C6V8-QX | BZX58550-C6V8-Q |
| 934662178115 | BZX58550-C6V8X   | BZX58550-C6V8   |
| 934663442115 | BZX58550-C7V5-QX | BZX58550-C7V5-Q |
| 934662179115 | BZX58550-C7V5X   | BZX58550-C7V5   |
| 934663443115 | BZX58550-C8V2-QX | BZX58550-C8V2-Q |
| 934662181115 | BZX58550-C8V2X   | BZX58550-C8V2   |
| 934663444115 | BZX58550-C9V1-QX | BZX58550-C9V1-Q |
| 934662182115 | BZX58550-C9V1X   | BZX58550-C9V1   |
| 934663060115 | MM5Z10VT5GF      | MM5Z10VT5G      |

|              |                 |                 |               |
|--------------|-----------------|-----------------|---------------|
| 934663061115 | MM5Z11VT5GF     |                 | MM5Z11VT5G    |
| 934663062115 | MM5Z12VT5GF     |                 | MM5Z12VT5G    |
| 934663063115 | MM5Z13VT5GF     |                 | MM5Z13VT5G    |
| 934663192115 | MM5Z15VT5GF     |                 | MM5Z15VT5G    |
| 934663193115 | MM5Z16VT5GF     |                 | MM5Z16VT5G    |
| 934663194115 | MM5Z18VT5GF     |                 | MM5Z18VT5G    |
| 934663195115 | MM5Z20VT5GF     |                 | MM5Z20VT5G    |
| 934663196115 | MM5Z22VT5GF     |                 | MM5Z22VT5G    |
| 934663197115 | MM5Z24VT5GF     |                 | MM5Z24VT5G    |
| 934663198115 | MM5Z27VT5GF     |                 | MM5Z27VT5G    |
| 934663181115 | MM5Z2V4T5GF     |                 | MM5Z2V4T5G    |
| 934663182115 | MM5Z2V7T5GF     |                 | MM5Z2V7T5G    |
| 934663199115 | MM5Z30VT5GF     |                 | MM5Z30VT5G    |
| 934663202115 | MM5Z33VT5GF     |                 | MM5Z33VT5G    |
| 934663204115 | MM5Z36VT5GF     |                 | MM5Z36VT5G    |
| 934663183115 | MM5Z3V0T5GF     |                 | MM5Z3V0T5G    |
| 934663184115 | MM5Z3V3T5GF     |                 | MM5Z3V3T5G    |
| 934663200115 | MM5Z3V6T5GF     |                 | MM5Z3V6T5G    |
| 934663201115 | MM5Z3V9T5GF     |                 | MM5Z3V9T5G    |
| 934663203115 | MM5Z4V3T5GF     |                 | MM5Z4V3T5G    |
| 934663205115 | MM5Z4V7T5GF     |                 | MM5Z4V7T5G    |
| 934663035115 | MM5Z5V1T5GF     |                 | MM5Z5V1T5G    |
| 934663036115 | MM5Z5V6T5GF     |                 | MM5Z5V6T5G    |
| 934663037115 | MM5Z6V2T5GF     |                 | MM5Z6V2T5G    |
| 934663038115 | MM5Z6V8T5GF     |                 | MM5Z6V8T5G    |
| 934663039115 | MM5Z7V5T5GF     |                 | MM5Z7V5T5G    |
| 934663040115 | MM5Z8V2T5GF     |                 | MM5Z8V2T5G    |
| 934663059115 | MM5Z9V1T5GF     |                 | MM5Z9V1T5G    |
| 934058512115 | PESD12VS1UB,115 |                 | PESD12VS1UB   |
| 934665519115 | PESD12VS1UB-QX  |                 | PESD12VS1UB-Q |
| 934058513115 | PESD15VS1UB,115 | PESD15VS1UB,115 | PESD15VS1UB   |
| 934664696135 | PESD15VS1UB-QF  |                 | PESD15VS1UB-Q |
| 934664696115 | PESD15VS1UB-QX  |                 | PESD15VS1UB-Q |
| 934058513135 | PESD15VS1UBF    |                 | PESD15VS1UB   |
| 934058514115 | PESD24VS1UB,115 |                 | PESD24VS1UB   |
| 934063221115 | PESD3V3L1UB,115 | PESD3V3L1UB,115 | PESD3V3L1UB   |
| 934058509115 | PESD3V3S1UB,115 |                 | PESD3V3S1UB   |
| 934664957115 | PESD3V3S1UB-QX  |                 | PESD3V3S1UB-Q |
| 934062952115 | PESD3V3U1UB,115 | PESD3V3U1UB,115 | PESD3V3U1UB   |
| 934063219115 | PESD5V0L1UB,115 | PESD5V0L1UB,115 | PESD5V0L1UB   |
| 934664968115 | PESD5V0L1UB-QX  |                 | PESD5V0L1UB-Q |
| 934058005115 | PESD5V0S1BB,115 |                 | PESD5V0S1BB   |
| 934058005335 | PESD5V0S1BB,335 |                 | PESD5V0S1BB   |
| 934664970135 | PESD5V0S1BB-QF  |                 | PESD5V0S1BB-Q |
| 934664970115 | PESD5V0S1BB-QX  |                 | PESD5V0S1BB-Q |
| 934058005135 | PESD5V0S1BBF    |                 | PESD5V0S1BB   |
| 934058511115 | PESD5V0S1UB,115 |                 | PESD5V0S1UB   |
| 934664959115 | PESD5V0S1UB-QX  |                 | PESD5V0S1UB-Q |

|              |                  |                  |               |
|--------------|------------------|------------------|---------------|
| 934060855115 | PESD5V0U1BB,115  | PESD5V0U1BB,115  | PESD5V0U1BB   |
| 934664967115 | PESD5V0U1BB-QX   |                  | PESD5V0U1BB-Q |
| 934060855315 | PESD5V0U1BBYL    |                  | PESD5V0U1BB   |
| 934062186115 | PESD5V0U1UB,115  |                  | PESD5V0U1UB   |
| 934664963115 | PESD5V0U1UB-QX   |                  | PESD5V0U1UB-Q |
| 934063245115 | PESD5V0V1BB,115  |                  | PESD5V0V1BB   |
| 934663867115 | PESD5V0V1BB-QX   | PESD5V0V1BB-QX   | PESD5V0V1BB-Q |
| 934064539115 | PESD5V0X1UAB,115 | PESD5V0X1UAB,115 | PESD5V0X1UAB  |
| 934064539315 | PESD5V0X1UABYL   |                  | PESD5V0X1UAB  |
| 934064538135 | PESD5V0X1UB,135  |                  | PESD5V0X1UB   |
| 934061268115 | PESD5Z12,115     |                  | PESD5Z12      |
| 934061263115 | PESD5Z2.5,115    |                  | PESD5Z2.5     |
| 934061264115 | PESD5Z3.3,115    |                  | PESD5Z3.3     |
| 934665526115 | PESD5Z3.3-QX     |                  | PESD5Z3.3-Q   |
| 934061265115 | PESD5Z5.0,115    |                  | PESD5Z5.0     |
| 934665527115 | PESD5Z5.0-QX     |                  | PESD5Z5.0-Q   |
| 934061265135 | PESD5Z5.0F       |                  | PESD5Z5.0     |
| 934061266115 | PESD5Z6.0,115    | PESD5Z6.0,115    | PESD5Z6.0     |
| 934061267115 | PESD5Z7.0,115    |                  | PESD5Z7.0     |
| 934665528115 | PESD5Z7.0-QX     |                  | PESD5Z7.0-Q   |
| 934057301115 | PMEG2005EB,115   | PMEG2005EB,115   | PMEG2005EB    |
| 934667796115 | PMEG2005EB-QX    |                  | PMEG2005EB-Q  |
| 934057757115 | PMEG2010AEB,115  |                  | PMEG2010AEB   |
| 934663806135 | PMEG2010AEB-QF   |                  | PMEG2010AEB-Q |
| 934663806115 | PMEG2010AEB-QX   |                  | PMEG2010AEB-Q |
| 934057757135 | PMEG2010AEBF     | PMEG2010AEBF     | PMEG2010AEB   |
| 934057098115 | PMEG3002AEB,115  |                  | PMEG3002AEB   |
| 934665831115 | PMEG3002AEB-QX   |                  | PMEG3002AEB-Q |
| 934057098135 | PMEG3002AEBF     |                  | PMEG3002AEB   |
| 934057098315 | PMEG3002AEBYL    |                  | PMEG3002AEB   |
| 934060117115 | PMEG3005EB,115   |                  | PMEG3005EB    |
| 934664911115 | PMEG3005EB-QX    |                  | PMEG3005EB-Q  |
| 934060116115 | PMEG3010EB,115   |                  | PMEG3010EB    |
| 934664916115 | PMEG3010EB-QX    | PMEG3010EB-QX    | PMEG3010EB-Q  |
| 934059739115 | PMEG4002EB,115   |                  | PMEG4002EB    |
| 934664291115 | PMEG4002EB-QX    |                  | PMEG4002EB-Q  |
| 934664291315 | PMEG4002EB-QYL   |                  | PMEG4002EB-Q  |
| 934060004115 | PMEG6002EB,115   |                  | PMEG6002EB    |
| 934664798135 | PMEG6002EB-QF    |                  | PMEG6002EB-Q  |
| 934664798115 | PMEG6002EB-QX    |                  | PMEG6002EB-Q  |
| 934060004135 | PMEG6002EBF      |                  | PMEG6002EB    |
| 934063954115 | RB520S30,115     | RB520S30,115     | RB520S30      |
| 934667745115 | RB520S30-QX      |                  | RB520S30-Q    |
| 934667745315 | RB520S30-QYL     |                  | RB520S30-Q    |
| 934063954315 | RB520S30YL       |                  | RB520S30      |
| 934063955115 | RB521S30,115     |                  | RB521S30      |
| 934666121135 | RB521S30-QF      |                  | RB521S30-Q    |
| 934666121115 | RB521S30-QX      |                  | RB521S30-Q    |

|              |               |               |              |
|--------------|---------------|---------------|--------------|
| 934063955315 | RB521S30YL    |               | RB521S30     |
| 934667862115 | RB530S40-QX   |               | RB530S40-Q   |
| 934667861115 | RB530S40X     |               | RB530S40     |
| 934061303115 | RB751S40,115  | RB751S40,115  | RB751S40     |
| 934665823115 | RB751S40-QX   |               | RB751S40-Q   |
| 934662389135 | SZMM5Z10VT5GF |               | SZMM5Z10VT5G |
| 934662391135 | SZMM5Z11VT5GF |               | SZMM5Z11VT5G |
| 934662392135 | SZMM5Z12VT5GF |               | SZMM5Z12VT5G |
| 934662393135 | SZMM5Z13VT5GF |               | SZMM5Z13VT5G |
| 934662394135 | SZMM5Z15VT5GF |               | SZMM5Z15VT5G |
| 934662395135 | SZMM5Z16VT5GF |               | SZMM5Z16VT5G |
| 934662396135 | SZMM5Z18VT5GF |               | SZMM5Z18VT5G |
| 934662397135 | SZMM5Z20VT5GF |               | SZMM5Z20VT5G |
| 934662398135 | SZMM5Z22VT5GF |               | SZMM5Z22VT5G |
| 934662399135 | SZMM5Z24VT5GF |               | SZMM5Z24VT5G |
| 934662401135 | SZMM5Z27VT5GF |               | SZMM5Z27VT5G |
| 934662372135 | SZMM5Z2V4T5GF |               | SZMM5Z2V4T5G |
| 934662373135 | SZMM5Z2V7T5GF |               | SZMM5Z2V7T5G |
| 934662402135 | SZMM5Z30VT5GF |               | SZMM5Z30VT5G |
| 934662403135 | SZMM5Z33VT5GF |               | SZMM5Z33VT5G |
| 934662404135 | SZMM5Z36VT5GF |               | SZMM5Z36VT5G |
| 934662374135 | SZMM5Z3V0T5GF |               | SZMM5Z3V0T5G |
| 934662375135 | SZMM5Z3V3T5GF |               | SZMM5Z3V3T5G |
| 934662376135 | SZMM5Z3V6T5GF |               | SZMM5Z3V6T5G |
| 934662377135 | SZMM5Z3V9T5GF |               | SZMM5Z3V9T5G |
| 934662378135 | SZMM5Z4V3T5GF |               | SZMM5Z4V3T5G |
| 934662381135 | SZMM5Z4V7T5GF |               | SZMM5Z4V7T5G |
| 934662382135 | SZMM5Z5V1T5GF |               | SZMM5Z5V1T5G |
| 934662383135 | SZMM5Z5V6T5GF |               | SZMM5Z5V6T5G |
| 934662384135 | SZMM5Z6V2T5GF | SZMM5Z6V2T5GF | SZMM5Z6V2T5G |
| 934662385135 | SZMM5Z6V8T5GF |               | SZMM5Z6V8T5G |
| 934662386135 | SZMM5Z7V5T5GF |               | SZMM5Z7V5T5G |
| 934662387135 | SZMM5Z8V2T5GF |               | SZMM5Z8V2T5G |
| 934662388135 | SZMM5Z9V1T5GF |               | SZMM5Z9V1T5G |

| BasicType_description               | PackageOutlineVersion_description |
|-------------------------------------|-----------------------------------|
| Schottky barrier single diode       | SOD523                            |
| GP Schottky Diodes                  | SOD523                            |
| Schottky barrier single diode       | SOD523                            |
| Schottky barrier single diode       | SOD523                            |
| Schottky barrier single diode       | SOD523                            |
| Schottky barrier single diode       | SOD523                            |
| Schottky barrier single diode       | SOD523                            |
| Schottky barrier single diode       | SOD523                            |
| Schottky barrier diode              | SOD523                            |
| Schottky barrier diode              | SOD523                            |
| Schottky barrier diode              | SOD523                            |
| Schottky barrier diode              | SOD523                            |
| Schottky barrier diode              | SOD523                            |
| General-purpose Schottky diodes     | SOD523                            |
| GP Schottky Diodes                  | SOD523                            |
| General-purpose Schottky diodes     | SOD523                            |
| General-purpose Schottky diodes     | SOD523                            |
| General-purpose Schottky diodes     | SOD523                            |
| General-purpose Schottky diodes     | SOD523                            |
| High-speed switching diodes         | SOD523                            |
| High-speed switching diodes         | SOD523                            |
| High-speed switching diodes         | SOD523                            |
| High-speed switching diodes         | SOD523                            |
| High-speed switching diodes         | SOD523                            |
| High-speed switching diodes         | SOD523                            |
| Single high-voltage switching diode | SOD523                            |
| Single high-voltage switching diode | SOD523                            |
| Single high-voltage switching diode | SOD523                            |
| switching diode                     | SOD523                            |
| switching diode                     | SOD523                            |
| switching diode                     | SOD523                            |
| High-voltage switching diode        | SOD523                            |
| High-voltage switching diode        | SOD523                            |
| High-voltage switching diode        | SOD523                            |
| High-voltage switching diode        | SOD523                            |
| Low-leakage diode                   | SOD523                            |
| Low IR Switching Diodes             | SOD523                            |
| Low-leakage diode                   | SOD523                            |
| Low-leakage diode                   | SOD523                            |
| Voltage regulator diodes            | SOD523                            |
| Voltage regulator diodes            | SOD523                            |
| Small Signal Zener Diode            | SOD523                            |
| Voltage regulator diodes            | SOD523                            |
| Voltage regulator diodes            | SOD523                            |
| Small Signal Zener Diode            | SOD523                            |
| Voltage regulator diodes            | SOD523                            |
| Voltage regulator diodes            | SOD523                            |

[illegible]

[illegible]

[illegible]

|                          |        |
|--------------------------|--------|
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Voltage regulator diodes | SOD523 |
| Voltage regulator diodes | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Small Signal Zener Diode | SOD523 |
| Small Signal Zener Diode | SOD523 |

[illegible]

[illegible]

[illegible]

[illegible]

|                                                                    |        |
|--------------------------------------------------------------------|--------|
| Low capacitance bidirectional ESD protection diode                 | SOD523 |
| Low capacitance bidirectional ESD protection diode                 | SOD523 |
| Low capacitance bidirectional ESD protection diode                 | SOD523 |
| Ultra low capacitance unidirectional ESD protection diodes         | SOD523 |
| Ultra low capacitance unidirectional ESD protection diodes         | SOD523 |
| Very low capacitance bidirectional ESD protection diode            | SOD523 |
| Very low capacitance bidirectional ESD protection diode            | SOD523 |
| Ultra low capacitance unidirectional ESD protection diode          | SOD523 |
| Ultra low capacitance unidirectional ESD protection diode          | SOD523 |
| Ultra low capacitance unidirectional ESD protection diode          | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low capacitance unidirectional ESD protection diodes               | SOD523 |
| Low VF MEGA Schottky barrier diode                                 | SOD523 |
| Low VF MEGA Schottky barrier diode                                 | SOD523 |
| 20 V, 1 A low VF MEGA Schottky barrier rectifier in SOD523 package | SOD523 |
| 20 V, 1 A low VF MEGA Schottky barrier rectifier in SOD523 package | SOD523 |
| 20 V, 1 A low VF MEGA Schottky barrier rectifier in SOD523 package | SOD523 |
| 20 V, 1 A low VF MEGA Schottky barrier rectifier in SOD523 package | SOD523 |
| Low VF MEGA Schottky barrier diode                                 | SOD523 |
| Low VF MEGA Schottky barrier diode                                 | SOD523 |
| Low VF MEGA Schottky barrier diode                                 | SOD523 |
| Low VF MEGA Schottky barrier diode                                 | SOD523 |
| 0.5 A very low VF MEGA Schottky barrier rectifier                  | SOD523 |
| 0.5 A very low VF MEGA Schottky barrier rectifier                  | SOD523 |
| 1 A very low VF MEGA Schottky barrier rectifier                    | SOD523 |
| 1 A very low VF MEGA Schottky barrier rectifier                    | SOD523 |
| 200 mA very low VF MEGA Schottky barrier rectifier                 | SOD523 |
| 200 mA very low VF MEGA Schottky barrier rectifier                 | SOD523 |
| 200 mA very low VF MEGA Schottky barrier rectifier                 | SOD523 |
| 0.2 A very low VF MEGA Schottky barrier rectifier                  | SOD523 |
| 0.2 A very low VF MEGA Schottky barrier rectifier                  | SOD523 |
| 0.2 A very low VF MEGA Schottky barrier rectifier                  | SOD523 |
| 0.2 A very low VF MEGA Schottky barrier rectifier                  | SOD523 |
| 200 mA low VF MEGA Schottky barrier rectifier                      | SOD523 |
| GP Schottky                                                        | SOD523 |
| GP Schottky                                                        | SOD523 |
| 200 mA low VF MEGA Schottky barrier rectifier                      | SOD523 |
| 200 mA low Vf MEGA Schottky barrier rectifier                      | SOD523 |
| Small Signal Schottky Diode                                        | SOD523 |
| Small Signal Schottky Diode                                        | SOD523 |

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

SalesItem\_source SalesItem\_lastTimeBuyDate SalesItem\_lastTimeShipDate





















SalesItem\_customerSpecificIndicator Replacement\_SalesItem\_orderablePartNumber

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

No

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

Replacement\_SalesItem\_name   Replacement\_ProductType\_name   Replacement\_BasicType\_description





















BusinessLine\_description

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

Bipolar Discretes

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

[illegible]

## Bipolar Discretes